

RU73X2A10KLTDF ✓ ACTIVE

Holsworthy | Holsworthy RU73


TE Internal #: 5-2176272-3

Surface Mount Resistors, Precision Resistor, 2 Termination, 0805, Taped & Reeled, .01 %, Thin Film, Resistance Class 1k Ω – 1M Ω , 10K Ω , Holsworthy RU73

[View on TE.com >](#)



Passive Components > Resistors > Surface Mount Resistors



Resistor Type: **Precision Resistor**

Number of Terminations: **2**

Package Size Code: **0805**

Packaging Method: **Taped & Reeled**

Passive Component Tolerance: **.01 %**

Features

Product Type Features

Product Type	Fixed Resistor
Resistor Type	Precision Resistor
Package Size Code	0805
Element Type	Thin Film

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Voltage Rating	100 V
Passive Component Tolerance	.01 %
Resistance Class	1k Ω – 1M Ω
Resistance Value	10K Ω
Power Rating	.1 W

Termination Features

Number of Terminations	2
------------------------	---

Surface Mount Resistor Termination Type	Solder
---	--------

Dimensions

Passive Component Dimensions	2 x 1.25 x .55 mm
------------------------------	-------------------

Usage Conditions

Temperature Coefficient	±3 ppm/°C
-------------------------	-----------

Packaging Features

Packaging Method	Taped & Reeled
------------------	----------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 5-2176270-9
RU 0805 100R 0.01% 2PPM 1K RL



TE Part # 7-2176270-6
RU 0805 150R 0.01% 2PPM 1K RL

Also in the Series | **Holsworthy RU73**



Surface Mount Resistors(757)

Customers Also Bought



TE Part #3-641215-2
02P MTA100 HDR ASSY FL/ST 30AU



TE Part #4-644511-3
03P MTA100 CONN ASSY ON TAPE



TE Part #1676227-2
RN 0805 1K24 0.1% 10PPM 1KRL



TE Part #8-1879208-0
CPF 0402 20K 0.1% 25PPM 1K RL



TE Part #1676222-3
RN 0805 1K13 0.1% 10PPM 5KRL



TE Part #2013595-1
INDUSTRIAL MINI I/O PLUG KIT D1



TE Part #181948-2
250 FASTON,TAB,TPBR



TE Part #8-2176271-9
RU 0805 2K21 0.01% 2PPM 1K RL



TE Part #EM7499-000
X4-0.8-0-SP-SM



Documents

Product Drawings

[RU 0805 10K 0.01% 2PPM 1K RL](#)

English

Datasheets & Catalog Pages

[Thin film chip resistor RU73 series](#)

English