

USB-C to USB-A Cable (M/M), USB 3.2 Gen 2 (10 Gbps), Thunderbolt 3 Compatible, 3 ft. (0.91 m)

MODEL NUMBER: U428-003-G2



Connects a computer, laptop, tablet, smartphone or other device with a USB-C port to a device or peripheral with a USB-A port.

Features

Supports USB 3.2 Gen 2

- Recommended for smartphones, tablets, laptops, computers, hard drives, chargers and other compatible devices
- Data transfer speeds up to 10 Gbps
- Backward compatible with previous USB generations

USB-C Male Connector

- Fumble-free reversible plug ensures fast, easy connection every time

Premium Construction for Superior Signal Transfer

- Foil and braid shielding for error-free signal quality and EMI/RFI protection
- Molded nickel-plated connectors and gold-plated contacts
- Integral strain relief for long life
- Rugged PVC jacket

Specifications

OVERVIEW	
UPC Code	037332197498
Device Compatibility	Amazon Kindle; Chromebook; Computer; Laptop; Phone; Tablet
Technology	USB 3.x
Country/Region	Global
Cable Type	Passive

Highlights

- USB 3.2 Gen 2 data transfer speeds up to 10 Gbps
- Reversible USB-C male connector for fast connection the first time
- Error-free signal quality and EMI/RFI protection
- Molded nickel-plated connectors and gold-plated contacts
- Backward compatible with previous USB generations

System Requirements

- Device with a USB-C port
- Device with a USB-A port

Package Includes

U428-003-G2 USB 3.2 Gen 2 (10 Gbps) Cable, USB-C to USB-A (M/M), 3 ft.

CHARGING	
Compatible Devices	Chromebook; Laptop; Smartphone; Tablet
PHYSICAL	
Material of Construction	PVC
Cable Jacket Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	4.5MM
Cable Length (ft.)	3
Cable Length (m)	0.91
Cable Length (in.)	36
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.12
Shipping Weight (kg)	0.05
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000
ENVIRONMENTAL	
Operating Temperature Range	14° to 140°F (-10° to 60°C)
Storage Temperature Range	-4° to 185°F (-20° to 85°C)
Relative Humidity	10 to 85% RH, Non-Condensing
CONNECTIONS	
Side A - Connector 1	USB A (MALE)
Side B - Connector 1	USB C (MALE)
Connector Plating	Nickel
Contact Plating	Gold
Connector Style	Straight
FEATURES & SPECIFICATIONS	
USB Specification	USB 3.2 Gen 2 (Up to 10 Gbps)
Data Transfer Rate	10 Gbps
STANDARDS & COMPLIANCE	
Product Certifications	ICES (Canada); NOM (Mexico)

Product Compliance	CE (Europe); REACH; RoHS; UKCA
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty