



300V 15A 28-12AWG 2.5mm²

Poles: 2-24P

Pitch: 5.0mm(.197")

Torque: 0.4N.m

Materials

Housing: PA66 (UL 94V-0)

Contact Phosphor Bronze, Nickel Plated.

Wire Cage: Brass (Nickel Plated) or Steel (zinc plated)

Screw: M2.5, Steel, A3 Zinc Plated.

设计/Designed by	绘图/Drawing by	审核/Checked by	批准/Approved by	未注公差 General Tolerance	
				x. ±0.2	x.° ±2°
				.x ±0.1	.x° ±1°
				.xx ±0.05	.xx° ±0.5°
				.xxx ±0.01	
		图名/Title	文件编号/File No.		
		XY2500FA-5.0 产品图	QJ/XYT-2270100		
		备注/Remark	页序/Sheet	单位/Units: mm	

序号/RevNo.	更改记录/Revision note	签名/Signature	日期/Date