



Keyword, Part Number or Cross-Ref

All Products Solutions Support

[Home](#) / [Products](#) / [Wire Routing, Management & Protection](#) / [Cable & Wire Ties, Mounts & Straps](#) / [Cable Bundling Straps & Tools](#) / [GS4MT-E](#)



GS4MT-E Stainless Steel Cable Tie Tool

Ergonomic, stainless steel cable tie installation tool.



Specifications













For Use With	MLT/S/LH/H/EH, MLTC/H, MLTFC/S/H or MLTDH/EH
Tool Type	Manual
Tension Type	Controlled Tension
Cut Off Type	Automatic
Overall Length (In.)	7.8
Overall Length (mm)	198.12
Overall Width (In.)	1.27
Overall Width (mm)	32.26

Overall Height (In.)	5.74
Overall Height (mm)	145.83
Color	Tan
UNSPSC	27112410
RoHS Compliancy Status	RoHS directive is not applicable
Min. Order Qty.	1
Product Category	Stainless Steel Cable Tie Tool
Product Type	Stainless Steel Cable Tie Tool

UPC	61305644920
Std. Pkg. Qty.	1
Std. Pkg. Volume (cf)	0.6320

Std. Ctn. Qty.	0
Std. Ctn. Volume (cf)	0.0000

Resources

Part Drawings	CD, GS4MT-E Customer Drawing	US English	PDF	380.41KB		
Product Bulletins	Fully Coated Stainless Steel Cable Ties Product Bulletin	US English	PDF	756.46KB		
Installation Documents	KGTS-ETL Tension Lockout Kit Installation Instructions For: GTS-E, GS2B-E, GTH-E, GS4H-E, GS4EH-E and GS4MT-E Tools	US English	PDF	163.94KB		
Product Bulletins	Panduit Permanent Identification System	US English	PDF	1.40MB		
Installation Documents	Stainless Steel Tie Installation Tool Operating Instructions: PA27730A02	US English	PDF	1.00MB		
Application Guides	Stainless Steel Application Guide -SSAG06--SA-ENG	US English	PDF	4.79MB		

Related Products



GS4MT

Installation tool for use with the following stainless steel cross section ties: Type MLT: Standard, light-heavy, and heavy Type MLTC, MLTFC, and MLTD:



MS10W50T15-L4

The Panduit Pan-Steel® Strap is designed to maintain a safe, secure connection. Built with 304 AISI stainless steel with a fold-over lock, it is ideal for indoor and outdoor conditions.



ST2MT

Installation tool for use with the following stainless steel cross section ties: Type MLT: Standard, light-heavy, heavy and extra-heavy Type MLTFC: Standard, heavy and extra-heavy Type

banding cross sections: Type MB:
Standard and heavy Type MBC:
Heavy

Low-profile buckle, 37"L
(940mm), 0.5" (13mm), Tensile
Strength: 2979, Bundle
diameter: 10" (254mm), 50pc.

MLTC and MLT-LPAL:
Heavy Type MLTD: Heavy and
extra-heavy Used with custom
length banding cross
sections: Type MB: Standard,
heavy and extra-heavy Type
MBC: Heavy and extra-heavy



Email Support

Email support available
24/7



800-777-3300

Monday through Thursday
7:00 am-6:30 pm CST
Friday 7:00 am-6:00 pm
CST



Where to Buy

Find a Panduit Distributor
or Partner

ABOUT US

Research and Development
Media Resources
World Headquarters
Awards
Partner Ecosystem
Panduit Code of Conduct

CAREERS AT PANDUIT

THE HUB – PARTNER PORTAL

PRODUCT REGISTRATION

PANDUIT CONNECTIONS BLOG



GET OUR CATALOG

Download the PDF or request a copy be
mailed to you.

Which catalog would you like? ▼

▶ DOWNLOAD ▶ REQUEST COPY

