

Search Results

- Evaluate
- FAQ's
- How to Buy
- Bill of Material
 - Favorite Products List
 - Locate Distributor


Home > Products Overview > Search Results >

Current refinements (click  to remove) Search Tips Within Results

 Text Search: 'F3X4IB6'

Your search criteria matched only one product, shown below

F3X4IB6



Choose from 29 sizes of *PANDUIT*® Type F Wiring Duct from 0.5" x 0.5" up to 4.0" x 5.0". Used for general purpose control panel wiring in communication closets. Ideal for use with high-density terminal blocks. The non-slip cover conceals all wiring and is easy to install. The duct and cover form a flush sidewall providing increased capacity and improved aesthetics.

Specifications

- Made of lead-free PVC
- UL Recognized continuous use temperature: 122°F (50°C)
- UL94 Flammability Rating of V-0
- Conforms with NFPA 79-2002 section 14.3.1 requirement for flame retardant material
- Available in Light Gray and White
- Provided with mounting holes

Features and Benefits

- Narrow finger/slot design allows further fanning of wires for neater wire management in high-density control panels
- *PANDUIT*® exclusive rounded edges protects hands and wiring/cablings from abrasion
- Non-slip cover stays in place during shipment, vibration and when in a vertical orientation, eliminating rework
- Flush cover design holds 10-12% more wires than traditional duct designs
- Double scoreline allows quick modification for larger cabling bundles saving installation time leading to a lower installed cost
- Specially formulated lead-free material eliminates health concerns associated with PVC that contains lead
- Double restricted slot design retains wire in slot for fast, easy wire installation or removal

Base and cover sold separately.

Part Number	F3X4IB6
RoHS Compliancy Status	Compliant
Part Description	Narrow slotted wiring duct.
Color	Intrinsic Blue
CSA Certified	Yes
Length (ft.)	6
CE Compliant	Yes
Duct Size W x H (In.)	3.25 x 4.10
Duct Size W x H (mm)	82.6 x 104.1
Mounting Method	Standard Mounting Holes
Pricing Description	Narrow Flush Cover With MTG Holes
Slot Width (In.)	0.20
Slot Width (mm)	5.0
Cover Part Number	C3IB6
Min. Order UOM	FT
Min. Order Qty.	6
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to Favorite Product List	<input type="checkbox"/>

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.