TAKACHI

268 HANDHELD CASES

292 UNIVERSAL ENCLOSURES

DEVELOPMENT BOARD ENCLOSURES

348

367
ROOM SENSOR ENCLOSURES


370

91 series IP67 low profile cases

Product overview

Beautifully designed low profile IP67 waterproof enclosures, ideal for tracking/monitoring in harsh environment

- IP67 rated, perfect for outdoor application
- White enclosures made from ASA UL94-HB plastic for high ultraviolet resistance
- Dark grey enclosures made from ABS UL94-V0 plastic for high flammability rating
- · Wall mount holes behind hinged caps for superior aesthetic finish
- Mounting kit accessory for easy mounting to poles, pillars, posts and lamp posts
- 91 series has been designed to meet the requirements of IP67





SPECIFICATION	
Material: Dark grey White grey	Base and lid ABS UL94-VO Base and lid ASA UL94-HB
Operating temperature	ABS, -10°C to +50°C ASA, -30°C to +60°C
Standard colours	Dark grey or white grey
Standard unit includes	Lid and base, gasket and fixing screws
Protection class	91 series has been designed to meet the requirements of IP67

DARK GREY	WHITE GREY	LENGTH	WIDTH	HEIGHT
WP5-7-2C	WP5-7-2G	65mm	52mm	18mm
WP5-7-3C	WP5-7-3G	65mm	52mm	27mm
WP8-8-2C	WP8-8-2G	75mm	75mm	22mm
WP8-8-4C	WP8-8-4G	75mm	75mm	35mm
WP6-8-2C	WP6-8-2G	80mm	60mm	20mm
WP6-8-3C	WP6-8-3G	80mm	60mm	30mm
WP8-10-2C	WP8-10-2G	100mm	75mm	22mm
WP8-10-4C	WP8-10-4G	100mm	75mm	35mm
WP10-10-3C	WP10-10-3G	100mm	100mm	25mm
WP10-10-4C	WP10-10-4G	100mm	100mm	40mm
WP9-13-3C	WP9-13-3G	130mm	90mm	25mm
WP9-13-4C	WP9-13-4G	130mm	90mm	40mm
WP11-15-3C	WP11-15-3G	150mm	110mm	27mm
WP11-15-4C	WP11-15-4G	150mm	110mm	40mm
WP13-18-5C	WP13-18-5G	175mm	130mm	45mm
WP13-18-3C	WP13-18-3G	175mm	135mm	30mm

KEY FEATURES

IP67 rated | Pole mounting kit accessory | Wall mount holes







268 HANDHELD CASES

UNIVERSAL ENCLOSURES

ACCESSORIES

Rubber feet 292



TAKACHI P/N	LENGTH	WIDTH	HEIGHT
PFRF-M2.5D	10mm	10mm	7.5mm

342

348
DEVELOPMENT
BOARD
ENCLOSURES

367 ROOM SENSOR ENCLOSURES

370

Pole mount kit



TAKACHI P/N	LENGTH	WIDTH	HEIGHT	DESCRIPTION
WPMB-M3D	18mm	14mm	9.5mm	Pole mount kit, dark grey
WPMB-M3G	18mm	14mm	9.5mm	Pole mount kit, white grey
WPMB-M4D	28mm	18mm	12mm	Pole mount kit, dark grey
WPMB-M4G	28mm	18mm	12mm	Pole mount kit, white grey

DARK GREY	WHITE GREY	WPMB-M3D	WPMB-M3G	WPMB-M4D	WPMB-M4G
WP5-7-2G	WP5-7-2G	•	•		
WP5-7-3G	WP5-7-3G	•	•		
WP8-8-2G	WP8-8-2G	•	•		
WP8-8-4G	WP8-8-4G	•	•		
WP6-8-2G	WP6-8-2G	•	•		
WP6-8-3G	WP6-8-3G	•	•		
WP8-10-2G	WP8-10-2G	•	•		
WP8-10-4G	WP8-10-4G	•	•		
WP10-10-3G	WP10-10-3G			•	•
WP10-10-4G	WP10-10-4G			•	•
WP9-13-3G	WP9-13-3G			•	•
WP9-13-4G	WP9-13-4G			•	•
WP11-15-3G	WP11-15-3G			•	•
WP11-15-4G	WP11-15-4G			•	•
WP13-18-5G	WP13-18-5G			•	•
WP13-18-3G	WP13-18-3G			•	•