

rotronic

Datenblatt - Fiche technique - Data sheet



11.04.5265



ROLINE VGA-Kabel HD15 ST – ST mit Ferritkern, 15m

ROLINE HD15 M/HD15 M avec noyaux de ferrite, 15m

ROLINE HQ VGA Cable with Ferrite, HD15 M – HD15 M, 15 m



NOTES:

- 1) P1 & P2 HD 15 Male / Male
- 2) FULLY COPPER FOIL SHIELD 360° P1 & P2.
- 3) CABLE JACKET : PVC BLACK COLOR
- 4) MOLDED HOOD : BLACK COLOR
- 5) REMOVED PIN 9, PIN 15 IS NOT CONNECTED
- 6) RoHS & REACH COMPLIANT
- 7) 2 x FERRITE CORE, BLACK COLOR

4	OUTER JACKET PVC 45Pa BLACK(1101) (RoHS)
3	INNER JACKET:PE (RoHS)
2	HDB15M BLUE SOLDER TYPE TERMINAL GOLD FLASH W/O 9 PIN (RoHS)
1	2919(28#1C+S+MY)3+26#7C+AEB(AL/MG) OD8.0MM 15000MM BLACK(1101) (RoHS)

UNLESS OTHERWISE SPECIFIED: DIMENSIONS ARE IN MILLIMETERS ANGULAR TOLERANCE: $\pm 0.0^\circ$	
DIMENSIONS	TOLERANCE
0.00 TO 30.00mm	± 0.10 mm
30.01 TO 80.00mm	± 0.13 mm
80.01 TO 150.00mm	± 0.15 mm
150.01mm	± 0.20 mm
MATERIAL	MATERIAL
FINISH	FINISH

rotronic

ROLINE HQ VGA Cable, w/Ferrite, HD 15 M/M, 15m, black				
11.04.5265				
SCALE /	SHEET 1 / 1	UNIT MM	SIZE A4	REV. A