



Similar to picture

Data**Technical Data****Control circuit**

| | |
|----------------------------------|---------------|
| Nominal input voltage U_N | 24 VDC |
| Input voltage range (high level) | 18 ... 30 VDC |
| Nominal input current at U_N | 7 mA |

Load circuit:

| | |
|----------------------------------|-------------------------|
| Circuit type | 2-conductor termination |
| Limiting continuous current | 3 A |
| Output voltage range | 0 ... 24 VDC |
| Max. voltage drop at output | ≤ 0.12 VDC |
| Reverse voltage transistor/triac | 33 V |

Safety and protection:

| | |
|---|------------------------|
| Dielectric strength, control/load circuit (AC, 1 min) | 3.75 kV _{rms} |
| Dielectric strength, control/load circuit (AC, 1 min) | 3.75 kV _{rms} |



Geometrical Data

| | |
|-------------------------|------------------|
| Width | 5 mm / 0.197 in |
| Height from the surface | 15 mm / 0.591 in |
| Depth | 28 mm / 1.102 in |

Mechanical data

| | |
|------------------|------------------|
| Type of mounting | Pluggable module |
|------------------|------------------|

Material Data

| | |
|--------|-------|
| Weight | 3.6 g |
|--------|-------|

Environmental Requirements

| | |
|--|----------------|
| Permissible surrounding air (operating) temperature at U_N | -30 ... 80 °C |
| Surrounding air (storage) temperature | -40 ... 100 °C |

Commercial data

| | |
|-------------------|---------------------------|
| Country of Origin | DE |
| GTIN | 4045454997632 |
| Product Group | 6 (Interface Electronics) |

Subject to changes.

WAGO Kontakttechnik GmbH & Co. KG
Hansastr. 27
32423 Minden
Phone: +49571 887-0 | Fax: +49571 887-169
Email: info.de@wago.com | Web: www.wago.com

Do you have any questions about our products?
We are always happy to take your call at 01788 568 008.