


PART NO. SEARCH - ENTER 3-4 CHARS:

Catalogs: [ASE](#) | [Metric](#) | [Handles & Ferrules](#)

- HOME
- PRODUCTS
- ONLINE CATALOG
- REQUEST QUOTE
- ORDER ONLINE
- CHECK STOCK
- REQUEST PRINT CATALOG
- REQUEST SAMPLES
- ENGINEERING DATA
- DISTRIBUTORS
- CAPABILITIES BROCHURE

CALL NOW:
203 888-2133

3/16 Hex Female Standoffs



[Home](#) [Previous](#) [Next](#)
[Related Metric](#)

Ordering Code			
XXXX	XXX	X	X
Length	Thread	Material	Finish

PART: **2057-440-SS**

Enter desired quantities:
Qty 1 Qty 2 Qty 3

[Download drawing](#)

Logos and links to MW Industries, ECIA, and NEFDA

Select	Part No.	Length
<input type="radio"/>	2051A	3/32
<input type="radio"/>	2051	1/8
<input type="radio"/>	2051T	5/32
<input type="radio"/>	2052	3/16
<input type="radio"/>	2052T	7/32
<input type="radio"/>	2053	1/4
<input type="radio"/>	2053T	9/32
<input type="radio"/>	2054	5/16
<input type="radio"/>	2054T	11/32
<input type="radio"/>	2055	3/8
<input type="radio"/>	2055T	13/32
<input type="radio"/>	2056	7/16
<input type="radio"/>	2056T	15/32
<input checked="" type="radio"/>	2057	1/2
<input type="radio"/>	2057T	17/32
<input type="radio"/>	2058	9/16
<input type="radio"/>	2058T	19/32
<input type="radio"/>	2059	5/8
<input type="radio"/>	2059T	21/32
<input type="radio"/>	2060	11/16
<input type="radio"/>	2060T	23/32

Select	Part No.	Length
<input type="radio"/>	2061	3/4
<input type="radio"/>	2061T	25/32
<input type="radio"/>	2062	13/16
<input type="radio"/>	2062T	27/32
<input type="radio"/>	2063	7/8
<input type="radio"/>	2063T	29/32
<input type="radio"/>	2064	15/16
<input type="radio"/>	2064T	31/32
<input type="radio"/>	2065	1"
<input type="radio"/>	2066	1-1/16
<input type="radio"/>	2067	1-1/8
<input type="radio"/>	2068	1-3/16
<input type="radio"/>	2069	1-1/4
<input type="radio"/>	2070	1-5/16
<input type="radio"/>	2071	1-3/8
<input type="radio"/>	2072	1-7/16
<input type="radio"/>	2073	1-1/2
<input type="radio"/>	2074	1-9/16
<input type="radio"/>	2075	1-5/8
<input type="radio"/>	2076	1-11/16
<input type="radio"/>	2077	1-3/4

Select	Part No.	Length
<input type="radio"/>	2078	1-13/16
<input type="radio"/>	2079	1-7/8
<input type="radio"/>	2080	1-15/16
<input type="radio"/>	2081	2"
<input type="radio"/>	2082	2-1/16
<input type="radio"/>	2083	2-1/8
<input type="radio"/>	2084	2-3/16
<input type="radio"/>	2085	2-1/4
<input type="radio"/>	2086	2-5/16
<input type="radio"/>	2087	2-3/8
<input type="radio"/>	2088	2-7/16
<input type="radio"/>	2089	2-1/2
<input type="radio"/>	2090	2-9/16
<input type="radio"/>	2091	2-5/8
<input type="radio"/>	2092	2-11/16
<input type="radio"/>	2093	2-3/4
<input type="radio"/>	2094	2-13/16
<input type="radio"/>	2095	2-7/8
<input type="radio"/>	2096	2-15/16
<input type="radio"/>	2097	3"

Select	Code	Thread
<input type="radio"/>	296	2-96
<input checked="" type="radio"/>	+40	+40

[Thread depth information](#)

Select	Code	Material	RoHS
<input type="radio"/>	AL	Aluminum	YES
<input type="radio"/>	B	Brass	YES
<input checked="" type="radio"/>	SS	Stainless Steel	YES
<input type="radio"/>	S	Steel	YES
<input type="radio"/>	N	Nylon	YES

[Material Specifications](#)

SELECT FINISH:

Plain Finish

* Finishes ending with an asterisk are not RoHS Compliant

[Ordering non-standard items](#)