

MINI DIN JACK Series




KLS1-294M MINI DIN Jack Solder assy with Cover Series

MATERIAL

- A. BOOT: PVC
- B. SHELL : ABS
- C. METAL SHIELD : BRASS NICKEL PLATED
- D. HOUSING : NYLON66+GLASS Fiber
- E. CONTACT : BRASS SILVER PLATED

Specification

1. RATION: 100V AC 1A MAX or 12V DC 2A MAX.
2. INSULATION RESISTANCE: 50M OHM MIN at 250V DC.
3. DIELECTRIC STRENGTH: 250 VAC / 1 MINUTE.
4. CONTACT RESISTANCE: 30M OHM MAX.
5. INSERTION FORCE: 4.5KG MAX.
6. WITHDRAWAL FORCE: 09.KG ~ 3KG.



○	7.0φ BACK SHELL
○	6.0φ BACK SHELL
⊗	5.0φ BACK SHELL (STANDARD)
□	COVER DIM.

TABLE A

ORDER INFORMATION

Product NO.: KLS1 - 294 - M 4 - B

Pos. NO.

MINI DIN Jack Solder assy with Cover Series

Color : B=Black G=Green P=Purple

Pin Number:
3=3P 4=4P 5=5P 6=6P 7=7P 8=8P
M=Male F=Female