


A12B1H10

Connection Type		with Terminal
Print		0-1 Marked
Product		Rocker Switch
Contact		1NO+1NO
Color		Black
Illumination		w/o Illumination
Dia		30*22mm
Current	Ie	16 A (250V AC)
Usage Category		AC15
Mechanical Life	Min Qty	50000
Electrical Life	Min Qty	50000
Operating Frequency	On-Off/Hour	Mech.900 Elec.900
Insulation Voltage	Ui	300 V
Impulse Withstand Voltage	Uimp	2.5 kV
Dielectric Strength (Body-Contact)		2.500V AC
Dielectric Strength (Contact-Contact)		1.500V AC
Isolation Resistance		10 MΩ min. (500V DC)
Operating Temperature		-25 / +80 °C
Pollution Degree		3
Protection Degree		IP20
Contact Material		AgNi
Cable Section		Terminal 6,3*0,8 mm
Short Circuit Breaking Capacity	Ics	1 kA
Serial		A12 Series
Body Color		Black Body
Specifications		With or w/o illumination options
		Four different color options
		Black or white body

Snap action

Standards / Certificates TS EN 61058-1

