



MA112

Connection Type	with Screw	
Print	On-On	
Product	Toggle Switch	
Contact	1NO+1NC	
Current	I_e	16 A (250V AC)
Usage Category	AC15	
Mechanical Life	Min Qty	100000
Electrical Life	Min Qty	10000
Operating Frequency	On-Off/Hour	Mech.900 Elec.900
Insulation Voltage	U_i	300V
Impulse Withstand Voltage	U_{imp}	2.5 kV
Dielectric Strength (Body-Contact)	2.500V AC	
Dielectric Strength (Contact-Contact)	1.500V AC	
Isolation Resistance	10 MΩ min. (500V DC)	
Operating Temperature	-25 / +80 °C	
Pollution Degree	3	
Protection Degree	IP20	
Contact Material	AgNi	
Cable Section	1-2.5 mm ²	
Screw Torque	1,5 Nm	
Short Circuit Breaking Capacity	I_{cs}	1 kA
Serial	MA Series	
Specifications	Maximum product reliability with V0 material	
	Different badge options	
Standards / Certificates	TS EN 61058-1	