



MBZS024S

Bulb Type		Led
Operating Current		20 mA
Operational Frequency		50 Hz
Operational Voltage		24V AC/DC
Product		Buzzer
Illumination		with LED
Dia		22 mm
Volume		90 dB
Power Consumption		0.6 W
Insulation Voltage	Ui	250 V
Operating Temperature		-15 / + 70 °C
Protection Degree		IP50
Cable Section		1.5-2.5 mm ²
Screw Torque		1,5 Nm
Serial		MB Series Plastic
Electrical Life	Min Hour	10000
Specifications		Non-flammable V0 PA6.6 contact blocks
		Monoblock strong body
		Finger safe protection

