


PDM11

Carton Box pieces	Qty	1
Product		Foot Switch
Model		with 1mt Cable
Contact		1CO
Color		Black
Current	Ie	6 A (250V AC)
Usage Category		AC 15
Mechanical Life	Min Qty	1000000
Electrical Life	Min Qty	100000
Operating Frequency	On-Off/Hour	Mech. 1800 Elec. 1200
Insulation Voltage	Ui	660V
Impulse Withstand Voltage	Uimp	2.5 kV
Dielectric Strength (Body-Contact)		2.500V AC
Dielectric Strength (Contact-Contact)		1.890V AC
Isolation Resistance		10 MΩ min. (500V DC)
Operating Temperature		-25 / +80 °C
Pollution Degree		3
Protection Degree		IP20
Contact Material		AgNi
Cable Section		1.5-2.5 mm ²
Screw Torque		1.5Nm
Short Circuit Breaking Capacity	Ics	1 kA
Body Material		Plastic
Serial		PDM Series
Specifications		Plastic
		Single speed
Standards / Certificates		TS EN 60947-5-1

CE

ERL

