

**Series 80 Mighty Mouse  
Backshells and Accessories**  
809S060, 809A060 and 809B060 Shrink Boots



**Lipped straight shrink boots-Type 1 high performance elastomer**

- 75° C to +165° C
- Excellent resistance to fuels, oils, solvents and heat.

Fully recovered boot shown. As supplied part will vary.



| Boot Size | Shell Size                     |            |            | Part Number<br>Pre-Coated with W1 Hi-Temp Hot-Melt Adhesive |
|-----------|--------------------------------|------------|------------|---|
|           | Series 800, 801, 802, 803, 804 | Series 805 | Series 811 |   |
| 1         | 5/6                            | 8          | 5          | 809S060-1   |
| 2         | 7                              | 9          | 6,7        | 809S060-2   |
| 3         | 8, 9                           | 10, 11     | 8,9        | 809S060-3   |
| 4         | 10, 11, 12, 13                 | 12, 15     | N/A        | 809S060-4   |
| 5         | 14, 15, 16, 17                 | 18, 19     | N/A        | 809S060-5   |
| 6         | 19, 21                         | 23         | N/A        | 809S060-6   |

**Lipped straight shrink boots- Type 2 zero halogen**

- Low Smoke, Zero Halogen
- Meets U.S. and E.U. toxicity requirements.

Fully recovered boot shown. As supplied part will vary.



| Boot Size | Shell Size                     |            |            | Part Number<br>Pre-Coated with W1 Hi-Temp Hot-Melt Adhesive |
|-----------|--------------------------------|------------|------------|---|
|           | Series 800, 801, 802, 803, 804 | Series 805 | Series 811 |   |
| 1         | 5/6                            | 8          | 5          | 809S060-1H  |
| 2         | 7                              | 9          | 6,7        | 809S060-2H  |
| 3         | 8, 9                           | 10, 11     | 8,9        | 809S060-3H  |
| 4         | 10, 11, 12, 13                 | 12, 15     | N/A        | 809S060-4H  |
| 5         | 14, 15, 16, 17                 | 18, 19     | N/A        | 809S060-5H  |
| 6         | 19, 21                         | 23         | N/A        | 809S060-6H  |

**Lipped 90° right angle shrink boots- Type 1 high performance elastomer**

- 75° C to +165° C
- Excellent resistance to fuels, oils, solvents and heat.

Fully recovered boot shown. As supplied part will vary.



| Boot Size | Shell Size                     |            |            | Part Number<br>Pre-Coated with W1 Hi-Temp Hot-Melt Adhesive |
|-----------|--------------------------------|------------|------------|---|
|           | Series 800, 801, 802, 803, 804 | Series 805 | Series 811 |   |
| 1         | 5/6                            | 8          | 5          | 809A060-1   |
| 2         | 7                              | 9          | 6,7        | 809A060-2   |
| 3         | 8, 9                           | 10, 11     | 8,9        | 809A060-3   |
| 4         | 10, 11, 12, 13                 | 12, 15     | N/A        | 809A060-4   |
| 5         | 14, 15, 16, 17                 | 18, 19     | N/A        | 809A060-5   |
| 6         | 19, 21                         | 23         | N/A        | 809A060-6   |

**Lipped 90° right angle shrink boots- Type 2 zero halogen**

- Low Smoke, Zero Halogen
- Meets U.S. and E.U. toxicity requirements.

Fully recovered boot shown. As supplied part will vary.



| Boot Size | Shell Size                     |            |            | Part Number<br>Pre-Coated with W1 Hi-Temp Hot-Melt Adhesive |
|-----------|--------------------------------|------------|------------|---|
|           | Series 800, 801, 802, 803, 804 | Series 805 | Series 811 |   |
| 1         | 5/6                            | 8          | 5          | 809A060-1H  |
| 2         | 7                              | 9          | 6,7        | 809A060-2H  |
| 3         | 8, 9                           | 10, 11     | 8,9        | 809A060-3H  |
| 4         | 10, 11, 12, 13                 | 12, 15     | N/A        | 809A060-4H  |
| 5         | 14, 15, 16, 17                 | 18, 19     | N/A        | 809A060-5H  |
| 6         | 19, 21                         | 23         | N/A        | 809A060-6H  |

**Lipped 45° angle shrink boots- Type 1 high performance elastomer**

- 75° C to +165° C
- Excellent resistance to fuels, oils, solvents and heat.

Fully recovered boot shown. As supplied part will vary.



| Boot Size | Shell Size                     |            | Part Number<br>Pre-Coated with W1 Hi-Temp Hot-Melt Adhesive |
|-----------|--------------------------------|------------|---|
|           | Series 800, 801, 802, 803, 804 | Series 805 |   |
| 1         | 5/6                            | 8          | 809B060-1   |
| 2         | 7                              | 9          | 809B060-2   |
| 3         | 8, 9                           | 10, 11     | 809B060-3   |
| 4         | 10, 11, 12, 13                 | 12, 15     | 809B060-4   |
| 5         | 14, 15, 16, 17                 | 18, 19     | 809B060-5   |
| 6         | 19, 21                         | 23         | 809B060-6   |

Dimensions in Inches (millimeters) are subject to change without notice.

