



FEP Flat Ribbon Cable

I.D.C.

Product Description

FEP (Fluorinated Ethylene Propylene) insulated conductors extruded in ribbon format for ease of termination with standard I.D.C.'s (Insulation Displacement Connectors).

Features & Benefits

- Extruded - Will Not Delaminate
- Tight Pitch Tolerances
- High Temp (200° C)
- Resistant to Chemicals
- Environmentally Stable
- High Performance Dielectric Insulation
- Non-combustible

Product Scope

Center Spacing	.050"	.025"	.0394" (1 mm)
Conductor	26 AWG, 7/34, SPC 26 AWG, 7/34 Bare 28 AWG, 7/36, SPC 28 AWG, 7/36 Bare	30 AWG, Solid, SPC 32 AWG, 7/40, SPC	28 AWG, 7/36, SPC
Signal Count	10 to 64	10 to 100	10 to 80

* For termination with standard I.D.C.'s

Specialty: Custom Constructions

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[F2807S-15-050-55](#) [F3007S-26-025-85](#) [F3007S-50-025-85](#) [F2807S-25-050-55](#) [F3007S-34-025-85](#) [F3007S-80-025-85](#) [F2807S-64-050-55](#) [F2807S-40-050-55](#) [F3007S-68-025-85](#) [F3007S-30-025-85](#) [F2807S-50-050-55](#) [F3007S-60-025-85](#) [F2807S-16-050-55](#) [F2807S-26-050-55](#) [F2807S-30-050-55](#) [F3007S-100-025-85](#) [F3007S-40-025-85](#) [F2807S-34-050-55](#) [F2807S-60-050-55](#) [100057-0025](#) [100057-0027](#) [100057-0033](#) [100057-0039](#) [100057-0024](#) [100057-0022](#) [100057-0040](#) [100057-0028](#) [100057-0037](#) [100057-0215](#) [100057-0182](#) [100057-0038](#) [100057-0035](#) [100057-0032](#) [100057-0023](#) [100057-0283](#) [100057-0036](#) [100057-0029](#) [100057-0026](#)