## 

S100LB2			
Bulb Type		Led	
Operating Current		6 mA	
<b>Operational Frequency</b>		50 Hz	
Operational Voltage		24V AC/DC	
Product		Pilot	
Color		White	
Illumination		with LED	
Dia		10 mm	
Power Consumption		0.2W	
Insulation Voltage	Ui	250 V	
Operating Temperature		-15 / + 70 °C	
Protection Degree		IP40	
Serial		S Series Plastic	
Electrical Life	Min Hour	10000	
Specifications	Ø10,14, 22 mm round types Different voltage variety		
	Connection facility with different terminal types		
CE			