

**S100LK2**

Bulb Type		Led
Operating Current		6 mA
Operational Frequency		50 Hz
Operational Voltage		24V AC/DC
Product		Pilot
Color		Red
Illumination		with LED
Dia		10 mm
Power Consumption		0.2W
Insulation Voltage	Ui	250 V
Operating Temperature		-15 / + 70 °C
Protection Degree		IP40
Serial		S Series Plastic
Electrical Life	Min Hour	10000
Specifications		Ø10,14, 22 mm round types
		Different voltage variety
		Connection facility with different terminal types

