

**S100LM2**

|                              |   |                  |
|------------------------------|---|------------------|
| <b>Bulb Type</b>             |   | Led              |
| <b>Operating Current</b>     |   | 6 mA             |
| <b>Operational Frequency</b> |   | 50 Hz            |
| <b>Operational Voltage</b>   |   | 24V AC/DC        |
| <b>Product</b>               |   | Pilot            |
| <b>Color</b>                 |   | Blue             |
| <b>Illumination</b>          |   | with LED         |
| <b>Dia</b>                   |   | 10 mm            |
| <b>Power Consumption</b>     |   | 0.2W             |
| <b>Insulation Voltage</b>    | <b>Ui</b>   | 250 V            |
| <b>Operating Temperature</b> |   | -15 / + 70 °C    |
| <b>Protection Degree</b>     |   | IP40             |
| <b>Serial</b>                |   | S Series Plastic |
| <b>Electrical Life</b>       | <b>Min Hour</b>                                   | 10000            |
| <b>Specifications</b>        | Ø10,14, 22 mm round types                         |                  |
|                              | Different voltage variety                         |                  |
|                              | Connection facility with different terminal types |                  |

