

**S100NK**

<b>Bulb Type</b>		Neon
<b>Operating Current</b>		0.4 mA
<b>Operational Frequency</b>		50 Hz
<b>Operational Voltage</b>		230V AC
<b>Product</b>		Pilot
<b>Color</b>		Red
<b>Dia</b>		10 mm
<b>Power Consumption</b>		0.25 W
<b>Insulation Voltage</b>	<b>Ui</b>	250 V
<b>Operating Temperature</b>		-15 / + 70 °C
<b>Protection Degree</b>		IP40
<b>Serial</b>		S Series Plastic
<b>Electrical Life</b>	<b>Min Hour</b>	10000
<b>Specifications</b>	Ø10,14, 22 mm round types	
	Different voltage variety	
	Connection facility with different terminal types	

