



S100NS

Bulb Type		Neon
Operating Current		0.4 mA
Operational Frequency		50 Hz
Operational Voltage		230V AC
Product		Pilot
Color		Yellow
Dia		10 mm
Power Consumption		0.25 W
Insulation Voltage	Ui	250 V
Operating Temperature		-15 / + 70 °C
Protection Degree		IP40
Serial		S Series Plastic
Electrical Life	Min Hour	10000
Specifications	∅10,14, 22 mm round types	
	Different voltage variety	
	Connection facility with different terminal types	

