S100NY			
Bulb Type		Neon	
Operating Current		0.4 mA	
Operational Frequency		50 Hz	
Operational Voltage		230V AC	
Product		Pilot	
Color		Green	
Dia		10 mm	
Power Consumption		0.25 W	
Insulation Voltage	Ui	250 V	
Operating Temperature		-15 / + 70 °C	
Protection Degree		IP40	
Serial		S Series Plastic	
Electrical Life	Min Hour	10000	
Specifications	Ø10,14, 22 mm round		
	Different voltage variety		
	Connection facility wi	th different terminal types	
CE			