

LED Flexi Tape High CRI



Key Features:

- Available in two different colour temperatures
- High CRI ≥ 90
- Supplied in 5M reels cuttable every 100mm
- 60 LEDs per metre
- Fitted with 3M Adhesive tape
- 3 years warranty


Lorem ipsum dolor sit amet, consectetur adipiscing elit. Terram, mihi crede, ea lanx et maria deprimet. Scio enim esse quosdam, qui quavis lingua philosophari possint; Quod dicit Epicurus etiam de voluptate, quae minime sint voluptates.

HIGH CRI SPECIFICATION

Model No.	C0-55-20-2-60-F3.5-20-FP	F0-55-20-2-60-F3.5-20-FP
Voltage	24VDC	24Vdc
Power Consumption	14.4W/M	14.4W/M
LED Qty	60 per mtr	60 per mtr
LED pitch	16.67mm	16.67mm
Cuttable	Every 100mm	Every 100mm
Colour Target	3000K	3000K
Luminous Flux	900lm/M	1080lm/M
IP Rating	IP20	IP20
Back Adhesive	3M adhesive tape	3M adhesive tape
Working temperature	-20°C ~ +40°C	-20°C ~ +40°C
Humidity	40% ~ 70% RH	40% ~ 70% RH
Dimensions	5000 x 3.5 x 1.0mm	5000 x 3.5 x 1.0mm



Mechanical



PowerLed (UK) Ltd
Orion House
Calleva Park
Aldermaston
Berkshire
RG7 8SN

Contact:
Tel: 0118 9703856
enquiries@powerled.uk.com
www.powerled.uk.com

