

PRODUCT DATASHEET

HALOSTAR STARLITE 35 W 12 V GY6.35

HALOSTAR STARLITE® 2000 | Low-voltage halogen lamps with pin base



Areas of application

- General illumination
- Entrance lighting
- Accent lighting
- Lighting for reading
- Garden lighting
- Shops
- Restaurants, hotels and similar prestigious applications
- Offices, public buildings
- Outdoor applications only in suitable luminaires

Product benefits

- Brilliant accent light
- Incredibly small dimensions for revolutionary new luminaire designs
- Approved for use in open luminaires (to IEC 60598-1)
- Axial filament for optimum directional light
- Special pins for corrosion protection
- UV filter
- Contains no mercury

Product features

- Average life: 2,000 h
- 100 % dimmable
- Color rendering index R_a : 100




TECHNICAL DATA

Electrical data

Nominal wattage	35 W
Construction wattage	35.00 W
Nominal voltage	12 V

Photometrical data

Luminous flux	580 lm
Luminous efficacy	16 lm/W
Light color (designation)	Warm White
Color temperature	2900 K
Color rendering index Ra	100
Light color	1029
UV protection	Yes



Light technical data

Starting time	0.0 s
---------------	-------

Dimensions & Weight

Overall length	44.00 mm
Light center length (LCL)	30,0 mm
Diameter	12 mm
Product weight	2.1 g

Lifespan

Lifespan	2000 h
Number of switching cycles	50000

Additional product data

Base (standard designation)	GY6.35
Mercury-free	Yes

Capabilities

Dimmable	Yes
Burning position	Any

Certificates & Standards

Energy efficiency class	G
Energy consumption	35.00 kWh/1000h

Country-specific categorizations



ILCOS	HSGST/C/UB-35-12-GY6.35-12/30
Order reference	64432 S

Energy labelling regulation data acc EU 2019/2015

Lighting technology used	OTHER
Non-directional or directional	NDLS
Mains or non-mains	NMLS
Light source cap-type (or other electric interface)	GY6.35
Connected light source (CLS)	No
Color-tuneable light source	No
Envelope	No
High luminance light source	No
Anti-glare shield	No
Correlated colour temperature type	SINGLE_VALUE
Claim of equivalent power	No
Length	44.00 mm
Height	12 mm
Width	12 mm
Chromaticity coordinate x	0.444
Chromaticity coordinate y	0.406
Beam angle correspondence	SPHERE_360
EPREL ID	714471
Model number	AC35300,AC35300,AC35300,AC35300



DOWNLOAD DATA

DOWNLOAD DATA	
	CAD data 3-dim
	CAD data 3-dim

LOGISTICAL DATA

Product code	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Gross weight	Volume
4058075094253	Folding box 1	25 mm x 23 mm x 70 mm	4.10 g	0.04 dm ³
4058075307810	Bundle 2	23 mm x 50 mm x 70 mm	9.00 g	0.08 dm ³
4058075094260	Shipping box 40	144 mm x 107 mm x 121 mm	205.00 g	1.86 dm ³
4058075307827	Shipping box 16	192 mm x 59 mm x 80 mm	110.00 g	0.91 dm ³
4058075307834	Shipping box 192	366 mm x 201 mm x 176 mm	1476.00 g	12.95 dm ³

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

DISCLAIMER

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.