




### 10 watt Power LED

Power: 10 watt  
 Current: 1050mA  
 CRI: >75 Max=95  
 Color: warm white,white,coolwhite,R-G-B,orange,purple,pink  
 Chip:Epistar,Bridgelux,semileds,Genesis etc  
 Application: Indoor and Outdoor Lights

1.PIC



2.Details :

Name	Model	Color	Angle (°)	wave length/Color (IF=1.05A)		Luminous flux (IF=1.05A)		Forward voltage (IF=1.050A)	
				MIN	MAX	MIN	MAX	MIN	MAX
10W LED	TDS-P010LRC11	RED	160	620nm	630nm	300	400	9	10
	TDS-P010LAD11	BLUE	160	460nm	465nm	150	200	9	10
	TDS-P010LAF17	GREEN	160	520nm	525nm	350	600	9	10
	TDS-P010LAG17	GREEN	160	525nm	530nm	350	600	9	10
	TDS-P010LAO17	WHITE	160	2000K	3000K	900	1000	9	12
	TDS-P010LAQ17	WHITE	160	3000K	4000K	900	1000	9	12
	TDS-P010LAS18	WHITE	160	4000K	5000K	900	1000	9	12
	TDS-P010LAU18	WHITE	160	5000K	6000K	900	1000	9	12
	TDS-P010LAW18	WHITE	160	6000K	7000K	900	1000	9	12
	TDS-P010LAY18	WHITE	160	7000K	8000K	900	1000	9	12
	TDS-P010L4Z18	WHITE	160	8000K	9000K	900	1000	9	12
	TDS-P010L4RGB	RGB	160	R=40LM	G=80LM	B=25LM	As per Data sheet		