




30 watt High Power LED

Power: 30 watt
 Current: 2100mA
 CRI: >75 Max=95
 Color: warm white, white, coolwhite, R-G-B, orange, purple, pink
 Chip: Epistar, Bridgelux, semileds, Genesis etc
 Application: Indoor and Outdoor Lights



Name	Model	Color	Angle (°)	wave length/Color (IF=2.1A)		Luminous flux (IF=2.1A)		forward voltage (IF=2.1A)	
				MIN	MAX	MIN	MAX	MIN	MAX
30W LED	TDS-P030LRC11	RED	160	620nm	625nm	300	400	12	15
	TDS-P030LAD18	BLUE	160	460nm	465nm	400	550	12	15
	TDS-P030LAF25	GREEN	160	520nm	525nm	1000	2200	15	17
	TDS-P030LAO27	WHITE	160	2000K	3000K	2000	2800	15	17
	TDS-P030LAQ27	WHITE	160	3000K	4000K	2000	2800	15	17
	TDS-P030LAS27	WHITE	160	4000K	5000K	2000	3000	15	17
	TDS-P030LAU27	WHITE	160	5000K	6000K	2000	3000	15	17
	TDS-P030LAW27	WHITE	160	6000K	7000K	2000	3000	15	17
	TDS-P030LAY27	WHITE	160	7000K	8000K	2000	3000	15	17
	TDS-P030LAZ27	WHITE	160	8000K	9000K	2000	3000	15	17
	TDS-P030L4RGB	RGB	160±5	R=40LM	G=80LM	B=25LM	As per Data sheet		