



#### Description

**3W / 9W / 10W / 20W / 30W / 50W High Power RGB LED For RGB Color Changing Light**

#### Quick Detail:

#### Features

- Color Changing: Red 620-630nm: 30-45lm/W Green: 80-90lm/W Blue: 20-25lm/W
- Led chip from Epistar and Bridgelux. 45X45MIL
- Very long operating life (up to 100k hours)
- Available in All colors Due to its color changing
- Low voltage DC 30-35V operated
- Cool beam, safe to the touch (180 degree)
- Connection: Different connections.
- Superior ESD protection
- RoHS compliant—lead-free

#### Applications:

All general Indoor lighting and outdoor lighting:

Wine Bar Light	under water lamp	Led flashing light	Led dancing light	Led aquarium light
under ground light	Traffic warning light	Led surgery light	Led garden light	Building light
Led flood light	Led landscape light	plant growing light	Led dancing light	Police car light

**Specifications:**

Product series	Product name	CCT	Luminous flux(lm)	Circuit Structure	Angle	Current(mA)
3W RGB / 9W RGB / 10W RGB / 30W RGB / 50W RGB / 100W RGB / 200-300W RGB LED (OEM Accepted)	30 watt rgb led	RGB	R:90-120	5 series 6 parallel	180	350
			G:200-300	5 series 6 parallel	180	350
			B:30-60	5 series 6 parallel	180	350
Notes: 1.The information here is just for your reference ; 2.Customized specification(such as : color , luminous , CRI , circuit structure and so on) can be accepted in our factory if we can reach them ;3.We are professional led manufacturer in China Jiangsu Province.						