


HEAT SHRINKABLE FULLY NYLON MALE CONNECTORS 熱收縮插鞘公端子

mm



ITEM NO.	DIMENSIONS					WIRE RANGE		COLOR
	B	L	t	dφ	Dφ	Twine mm ²	AWG	
HSRM250	6.3	38.5	0.8	1.8	3.9	0.75~1.25	18~16	RED
HSBM250	6.3	39.5	0.8	2.4	4.2	1.25~2.0	16~14	BLUE
HSYM250	6.3	39.5	0.8	3.5	5.5	2.63~6.64	12~10	YELLOW



HEAT SHRINKABLE FULLY NYLON FEMALE CONNECTORS 熱收縮插鞘母端子

mm



ITEM NO.	DIMENSIONS					WIRE RANGE		COLOR
	B	L	t	dφ	Dφ	Twine mm ²	AWG	
HSRF250	6.7	36.5	0.8	1.8	3.9	0.75~1.25	18~16	RED
HSBF250	6.7	36.5	0.8	2.4	4.2	1.25~2.0	16~14	BLUE
HSYF250	6.7	37	0.8	3.5	5.5	2.63~6.64	12~10	YELLOW

