

Multifunction Switch Power



PS3010HB



Features as switch power supply

- Long period continuously working under 300W
- User-friendly operation panel design
- Inbuilt output switch
- Outstanding EMI performance
- 5V/DC 2A compatible smart recognition power charger

Features as power charger

- Suitable for 12V and 24V battery charging with repair function
- Widely applied for charging battery from 10 to 120AH respectively
- Charging process without manual intervention
- Comprehensive protection procedure during the charging

Specifications

Input Voltage	AC 190V - 240V 50Hz ± 2Hz
Output Voltage	0 - 30V (conti. adj.)
Output current	0 - 10A (conti. adj.)
Supply Regulation	CV ≤ 1% + 10mV
Load Regulation	CV ≤ 1% + 5mV
Ripple	50mVp - p
Protection	Current Limit
Operating Time	8hr. conti
Dimensions (WxHxD)	178x240x90 mm
Weight	2.5 kgs