

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0190750024**
Status: **Active**
Overview: Solderless Terminals
Description: InsulKrimp Steel Star Ring Tongue Terminal for 14-16 AWG Wire, Stud Size 10 (M5), Mylar Tape Carrier

Documents:

3D Model	Product Specification PS-19902-009-001 (PDF)
Drawing (PDF)	Product Specification PS-19902-011-001 (PDF)
3D Model (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification

CSA	LR18689
UL	E32244

General

Product Family	Ring and Spade Terminals
Series	<u>19075</u>
Crimp Quality Equipment	Yes
Overview	<u>Solderless Terminals</u>
Product Name	InsulKrimp
Type	Ring
UPC	800753079854

Physical

Barrel Type	Closed
Color - Resin	Natural
Flammability	94V-0
Insulation	PVC
Material - Plating Mating	Tin
Net Weight	0.630/g
Packaging Type	Adhesive Tape on Reel
Stud Size	10 (M5)
Wire Insulation Diameter	4.45mm
Wire Size AWG	14, 16

Material Info

Engineering Number	SRB-S-229-10XT
--------------------	----------------

Reference - Drawing Numbers

Product Specification	PS-19902-009-001, PS-19902-011-001
-----------------------	------------------------------------



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

19075 Series

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
-------------	-----------

ATP Crimp Dies for the Tape Crimp Module and ATP-101 & 301 Press	<u>192880135</u>
Mini-Mac Applicator for Star Ring Terminals, 14-16 AWG Wire	<u>638852900</u>