

## Heater Series CSK 060

**Art.-No. 06030.1-00**

(Standard version: 06030.0-00)

### Important data



#### 1. Mecha. data<sup>1)</sup>

Housing: no difference

Connection: no difference

#### 2. Technical data<sup>1)</sup>

Operating voltage: 24V AC/DC (min. 12V; max. 30V)<sup>2)</sup>

Heating capacity: no difference  
(20W)

Inrush current max.: 8.0A

Operating temperature: -20 to +70°C (-4 to +158°F)

Pre-fuse: 6.3A T (time-delay)

Approval: VDE, EAC

---

<sup>1)</sup> data that vary compared to the standard version

<sup>2)</sup> Operating with voltages below 15V AC/DC reduces heating performance by approx. 10%.