

5

4

3

2

1

受控 CONTROLLED DOCUMENT

编号 P/N	40-9515HDS-CUST (SEE TABLE I)	版本 Rev	01	日期 Rel'd Date	Jul11,11
-----------	----------------------------------	-----------	----	------------------	----------

Description: 95 series solder panel & cable mount high density D-Sub connectors

Part No: 40-9515HDS

Application: 95 Series D-Sub Connector

Crimp Tool: N/A

Impedance: N/A

Frequency Range: N/A

Material: Shell Steel, Tin plated

Insulator PBT+30% Fiber-grass

UL94-V0 White

Contact Copper-alloy, Gold-flashed plated

RoHS Compliance: Yes

Technical Detail: N/A




TABLE I

Part Number	Description	A (mm)	B (mm)	C (mm)	D (mm)
40-9515HDS	FEMALE – SOCKET, SOLDER TYPE	30.80	24.99	16.34	19.20
40-9526HDS	FEMALE – SOCKET, SOLDER TYPE	39.20	33.32	24.70	27.70

DRAWING NO.
40-9515HDS-CUST(SEE TABLE I)

REVISIONS

01	OFFICIAL RELEASE
03-09-11	J J J D



DIM OUTLINE

CUSTOMER COPY



TITLE
95 SERIES SOLDER PANEL & CABLE MOUNT
HIGH DENSITY D-SUB CONNECTORS

SHEET 1 OF 1
DRAWING NO. 40-9515HDS-CUST
(SEE TABLE I)
SIZE A

TOLERANCE UNLESS OTHERWISE SPECIFIED		DRAWN BY JEAN.JIN	DATE 03-09-11
DECIMALS	mm	CHECKED BY JEAN.JIN	DATE 03-09-11
X	± 0.5	APPROVED BY DONALD	DATE 03-09-11
X.X	± 0.3		
X.XX	± 0.15		
ANGLES	± 0.5°	U/M	mm

THIS DRAWING WAS PRODUCED BY COMPUTER,
DO NOT SCALE DRAWING OR UPDATE MANUALLY.

5

4

3

2

1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cinch Connectivity Solutions:](#)

[40-9515HDS](#) [40-9526HDS](#)