


Rating: DC 24V 3A  
 Contact Resistance: 100 mΩ Max.  
 Operating temperature: -20°C ~ 70°C  
 Operating force: 3-20N  
 Operating Life: 5,000 cycles

Model No.	1	2
PIN	φ2.0	φ2.5



ITEM	PART NAME	TERN.O.	QTY.	MATERIAL	FINISHING	REMARK
②	Terminal	—	3	Phosphor bronze	Ag Plating	—
①	Housing	—	1	Nylon	Black	—

APPROVALS	DATE	TITLE:
DRAWN J.X.Zhang	2013/11/11	DC JACKES
CHECKED		DC-005C
APPROVALS		PART NO. DC-005C

**HRON**  
 ELECTRONICS CO.,LTD

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			
TOLERANCES ARE						
			30 <sup>±0.15</sup>	±0.30	ANGLE	
			10 <sup>±0.10</sup>	±0.20	UNIT: mm	SCALE: 1:1
			5 <sup>±0.10</sup>	±0.15	±Z'	DRAWING NO.
			~ 5	±0.10		PROJ.
						SHEET 1 OF 1