


G ; 2+ ; Valide


**MATERIAL:**  
 Body : Polyamid UL94 V-0  
 Elastomer link: Elastomer  
 Eyelet : brass tin plated  
**NOTES :**  
 -Operating temperature : -40° up to +105°  
 -This cap is a water and dust protected version.  
 -Level sealing : IP68 (1bar during 1 week)  
 -Pull out force of the crimped eyelet on the elastomer link : 10 N mini.



PART NUMBER	Ø A	B	C <sup>+0</sup> <sub>-6</sub>
UTS8DCGE	22.50	16.50	89
UTS10DCGE	26.20	18.40	108
UTS12DCGE	29.70	19.60	108
UTS14DCGE	34.60	21.50	105
UTS18DCGE	42	23	105

Country	Jurisdiction & Control List
FR	NOT LISTED

**P/N : UTSXXDCGE**



G	19/03/2018	Change dimension C		--
ISS	DATE	Latest modification - by: ROUILLARD Ch		MOD N°
Designed by: <b>ROUILLARD</b>		Date: 22/01/09	CUSTOMER DRAWING	
TITLE		UTS RECEPTACLE SEALING CAP WITH SMALL EYELET FOR SQUARE FLANGE RECEPTACLE		
Scale	2/1	General linear Tolerances: ± 0.4	NPRDS / PROJECT UTS1	
<b>SOURIAU</b>		<b>WWW.SOURIAU.COM</b>		This document is the property of SOURIAU It must not be reproduced or communicated without permission
FORMAT	<b>A3</b>	SOURIAU DRG N° C075-UTS1-A		SHEET 1 / 1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Souriau:](#)

[UTS8DCGE](#) [UTS10DCGE](#) [UTS12DCGE](#) [UTS14DCGE](#) [UTS18DCGE](#)