



AS25042 and AS25043 Protective Plug and Receptacle Covers

MATING CONNECTOR

AS50151

Basic Part Number

MS25042 = Plug Cover
MS25043 = Receptacle Cover

Shell Size
(Table I)


Finish

D = Cadmium, O.D.
DA = Black Anodize


MS25042

- 20

D



MS25042 Plug Cover



MS25043 Receptacle Cover

TABLE I: Shell Size, Thread, Attachment and Dimensions

| Shell Size | E Thread | F Dia Max | G Max | H Max | J Max | K Attachment Length (Inches) | L Dia Min | M Dia Min |
|------------|----------------|--------------|-------------|--------------|-------------|------------------------------|------------|------------|
| 8 | 1/2- 28 UNEF | .562 (14.3) | .656 (16.7) | .688 (17.5) | .469 (11.9) | 4.00 (101.6) | .151 (3.8) | .135 (3.4) |
| 10 | 5/8- 24 UNEF | .687 (17.4) | .656 (16.7) | .815 (20.7) | .469 (11.9) | 4.00 (101.6) | .151 (3.8) | .135 (3.4) |
| 12 | 3/4- 20 UNEF | .812 (20.6) | .844 (21.4) | 1.000 (25.4) | .469 (11.9) | 4.50 (114.3) | .151 (3.8) | .135 (3.4) |
| 14 | 7/8- 20 UNEF | .937 (23.8) | .844 (21.4) | 1.125 (28.6) | .469 (11.9) | 4.50 (114.3) | .151 (3.8) | .135 (3.4) |
| 16 | 1- 20 UNEF | 1.062 (27.0) | .844 (21.4) | 1.188 (30.2) | .469 (11.9) | 4.50 (114.3) | .151 (3.8) | .135 (3.4) |
| 18 | 1 1/8- 18 UNEF | 1.187 (30.1) | .844 (21.4) | 1.344 (34.1) | .469 (11.9) | 4.50 (114.3) | .151 (3.8) | .135 (3.4) |
| 20 | 1 1/4- 18 UNEF | 1.312 (33.3) | .844 (21.4) | 1.469 (37.3) | .469 (11.9) | 5.00 (127.0) | .182 (4.6) | .135 (3.4) |
| 22 | 1 3/8- 18 UNEF | 1.437 (36.5) | .844 (21.4) | 1.594 (40.5) | .469 (11.9) | 5.00 (127.0) | .182 (4.6) | .135 (3.4) |
| 24 | 1 1/2- 18 UNEF | 1.562 (39.7) | .844 (21.4) | 1.719 (43.7) | .469 (11.9) | 5.50 (139.7) | .182 (4.6) | .166 (4.2) |
| 28 | 1 3/4- 18 UNS | 1.812 (46.0) | .844 (21.4) | 1.969 (50.0) | .531 (13.5) | 7.75 (196.9) | .182 (4.6) | .166 (4.2) |
| 32 | 2- 18 UNS | 2.062 (52.4) | .844 (21.4) | 2.219 (56.4) | .531 (13.5) | 7.75 (196.9) | .213 (5.4) | .182 (4.6) |
| 36 | 2 1/4- 16 UN | 2.312 (58.7) | .844 (21.4) | 2.469 (62.7) | .531 (13.5) | 7.75 (196.9) | .213 (5.4) | .182 (4.6) |
| 40 | 2 1/2- 16 UN | 2.562 (65.1) | .844 (21.4) | 2.719 (69.1) | .531 (13.5) | 7.75 (196.9) | .213 (5.4) | .182 (4.6) |
| 44 | 2 3/4- 16 UN | 2.812 (71.4) | .844 (21.4) | 2.969 (75.4) | .531 (13.5) | 7.75 (196.9) | .213 (5.4) | .182 (4.6) |
| 48 | 3- 16 UN | 3.062 (77.8) | .844 (21.4) | 3.188 (81.0) | .531 (13.5) | 7.75 (196.9) | .213 (5.4) | .182 (4.6) |

APPLICATION NOTES

1. Assembly identified with manufacturer's name and part number, space permitting.
2. For complete dimensions, see the applicable Military Specification.
3. Metric dimensions (mm) are in parentheses.

Dimensions in inches (millimeters) and are subject to change without notice.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Glenair:

[MS25042-12DA](#) [MS25042-16D](#) [MS25042-22D](#) [MS25042-24D](#) [MS25042-32D](#) [MS25042-36D](#) [MS25042-36DA](#)
[MS25042-40DA](#) [MS25042-44D](#) [MS25042-44DA](#) [MS25042-48D](#) [MS25042-48DA](#) [MS25042-8D](#) [MS25042-8DA](#)
[MS25043-10D](#) [MS25043-36D](#) [MS25043-36DA](#) [MS25042-10D](#) [MS25042-10DA](#) [MS25042-12D](#) [MS25042-14D](#)
[MS25042-16DA](#) [MS25042-18D](#) [MS25042-18DA](#) [MS25042-20D](#) [MS25042-20DA](#) [MS25042-22DA](#) [MS25042-24DA](#)
[MS25042-28D](#) [MS25042-28DA](#) [MS25042-32DA](#) [MS25042-40D](#) [MS25043-10DA](#) [MS25043-16D](#) [MS25043-16DA](#)
[MS25043-18D](#) [MS25043-18DA](#) [MS25043-20D](#) [MS25043-22D](#) [MS25043-24D](#) [MS25043-24DA](#) [MS25043-28DA](#)
[MS25043-32D](#) [MS25043-32DA](#) [MS25043-14D](#) [MS25043-14DA](#) [MS25043-22DA](#) [MS25043-20DA](#) [MS25043-28D](#)
[MS25042-14DA](#) [MS25043-48D](#) [MS25043-40D](#) [MS25043-40DA](#) [MS25043-44DA](#) [MS25043-8D](#) [MS25043-12D](#)
[MS25043-48DA](#) [MS25043-8DA](#) [MS25043-44D](#) [MS25043-12DA](#)