

Han 6B cover plastic/SL/HBM, HSM, HCC



Part number	09 30 006 5405
Specification	Han 6B cover plastic/SL/HBM, HSM, HCC
HARTING eCatalogue	https://b2b.harting.com/09300065405

Image is for illustration purposes only. Please refer to product description.

Identification

Category	Accessories
Series of hoods/housings	Han [®] B
Type of hood/housing	Protection cover
Description of hood/housing	for bulkhead mounted housings for surface mounted housings Thermoplastic
Туре	Low construction High construction

Version

Size	6 B
Locking type	Single locking lever

Technical characteristics

Limiting temperature	-40 +125 °C
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4
	4X
	12

Material properties

RoHS	compliant
ELV status	compliant
China RoHS	е
REACH Annex XVII substances	Not contained

Page 1 / 2 | Creation date 2022-11-11 | Please note that the data specified here were taken as extracts from the online catalogue. Please refer to the user documentation for the complete and up-to-date information and data. Please also note that the user is responsible for validating functionality, conformity with applicable laws and directives, as well as for the electrical safety in the particular application.

HARTING Stiftung & Co. KG | Marienwerderstr. 3 | 32339 Espelkamp | Germany



Material properties

REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

Specifications and approvals

Approvals DNV GL

Commercial data

Packaging size	1
Net weight	18.8 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140161603
eCl@ss	27440208 Cap for industrial connectors