


THIS IS ISSUED IN STRICT CONFIDENCE THAT IT IS NOT USED AS A BASIS FOR MANUFACTURE OR SALE AND THAT IT IS NOT COPIED, REPRINTED OR DISCLOSED TO A THIRD PARTY EITHER WHOLLY OR IN PART WITHOUT THE PRIOR WRITTEN CONSENT OF CAL TEST ELECTRONICS, INC.

NOTES:

- SPECIFICATION:  
 JACKET: PVC. MULTI-LAYER, 1ST LAYER WHITE; 2ND LAYER "COLOR"  
 OD: .106±.008 (2.7 mm)  
 CONDUCTOR: BARE COPPER, STRANDING 130 x 0.07 mm = 0.50 mm<sup>2</sup>, 20 AWG.
- RATING:  
 VOLTAGE: 1,000 V CAT IV PER IEC 61010-031  
 CURRENT: 10 A MAX.  
 TEMPERATURE: -20° C TO +80° C.
- AVAILABLE IN 3 STANDARD LENGTHS AND 6 COLORS - SEE MODEL NUMBER BELOW.

REVISIONS			
REV.	DESCRIPTIONS	DATE	APPROVED
-	CLASS A RELEASED	7/11/99	
A	UPDATED FORMAT w/ CAGE CODE	4/18/04	



**MODEL NUMBER**

**CT2879-#-XXX**

COLOR: 0 - BLACK  
 2 - RED  
 4 - YELLOW  
 5 - GREEN  
 6 - BLUE  
 9 - WHITE

LENGTH: 10 - 10 m PACKAGE  
 50 - 50 m SPOOL  
 100 - 100 m SPOOL

THIRD ANGLE PROJECTION		UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE: FRACTIONS DECIMALS ± 1/32 .XX ± .02 .XXX ± .005 DO NOT SCALE DRAWING	CONTRACT NO.		<b>Cal Test Electronics</b> 22820 Savi Ranch Parkway Yorba Linda, CA 92887-4610			
			APPROVALS	DATE	TITLE			
MATERIAL		DRAWN	WDH	7/11/99	WIRE, TEST LEAD, PVC JACKET, 0.50 mm <sup>2</sup> , 20 AWG, 10 A			
FINISH		CHECKED			SIZE	CAGE CODE	DWG. NO.	REV.
NEXT ASSY	USED ON	ENGR.			A	43F45	P287900	A
APPLICATION		DESIGN ACTIVITY			SCALE	NONE	SHEET	1 OF 1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Cal Test Electronics:

[CT2879-2-100](#) [CT2879-6-10](#) [CT2879-4-100](#) [CT2879-4-50](#) [CT2879-2-10](#) [CT2879-0-100](#) [CT2879-5-50](#) [CT2879-0-10](#) [CT2879-5-10](#) [CT2879-9-100](#) [CT2879-4-10](#) [CT2879-6-100](#) [CT2879-9-50](#) [CT2879-2-50](#) [CT2879-6-50](#) [CT2879-9-10](#) [CT2879-0-50](#) [CT2879-5-100](#)