



Power wires 14 AWG, 105°C, 600V minimum, 6inch, cooper stranded; Polarity: Line=Black, Load=Red, Neutral=White

Signal wires 18 AWG, 105°C, 600V minimum, 6inch, cooper stranded; the positive dimming conductor shall have an insulation which is violet in color and the reference dimming conductor shall have an insulation which is gray in color. With other 2 wires to orange and brown

Note: 1. The socket material: PET, Add an UV stabilizer, UL 94V-0 RATED
 2. Copper contact materials: brass H62
 Terminal pin material: copper alloy 0.25 thick nickel underplate. contactpad 0.127um min thick gold paltd

						上海朗骏智能科技股份有限公司		
标记	处数	分区	更改文件号	签名	年、月、日			
设计			标准化			阶段标记	重量	比例
审核								1:1.3
工艺			批准			共	张	第
						张	第	张
						JL-JL240TXA1406R7P		