

Han 1A-HBM



Part number	09 10 000 0300
Specification	Han 1A-HBM
HARTING eCatalogue	https://b2b.harting.com/09100000300

Identification

Category	Hoods/Housings
Series	Han [®] 1 A
Type of hood/housing	Bulkhead mounted housings
Description of hood/housing	Straight

Version

Size	1 A
Details	Use 2x fixing screws M3

Technical characteristics

Limiting temperature	-30 ... +90 °C
Tightening torque	0.3 Nm Screws M3
Number of relockings	<10
Degree of protection acc. to IEC 60529	IP65

Material properties

Material (hood/housing)	Polyamide
Colour (hood/housing)	RAL 9005 (jet black)
Material (seal)	TPE
Colour (seal)	Yellow
Material flammability class acc. to UL 94	V-0

Specifications and approvals

Specifications	EN 45545-2 R22: HL1, HL2, HL3
	EN 45545-2 R23: HL1, HL2, HL3
	EN 45545-2 R24: HL1, HL2, HL3
	EN 61373 Cat 1B
Approvals	DNV GL



Pushing Performance

Commercial data

Packaging size	1
eCl@ss	27440202 Shell for industrial connectors