

432ERS6W

Wall mounted socket

2CMA101253R1000



Wall mounted outlet, 3P+N+E, 32A, 200/346 ... 240/415 V
 Clock Position Of Grounding Contact 6 hour Color code Red

GENERAL

| | |
|----------------------------|--|
| Product Name | Wall mounted socket |
| Product ID | 2CMA101253R1000 |
| Function | Wall mounted socket |
| EAN | 73926912539 |
| Catalog Description | Wall mounted outlets, 3P+N+E, 32A, 200/346 ... 240/415 V |
| Country of Origin | Czech Republic (CZ) |
| E-Number Finland | 2420165 |
| E-Number Norway | 1540747 |
| E-Number Sweden | E2417648 |
| Standards | IEC 60309-1, -2 |
| RoHS Status | Following EU Directive 2011/65/EU |

TECHNICAL

| | |
|-----------------------------|--------------------------|
| Product Main Type | ERS |
| Color | Red |
| Number of Poles | 5 |
| Clock Position | 6Hour |
| Rated Current | 32 ampere |
| Rated Voltage | 200/346 ... 240/415 volt |
| Frequency | 50 hertz 60 hertz |
| Degree of Protection | IP67 |
| Cable Cross-Section | 2.5...6 mm ² |
| Housing Material | Plastic (PA) |
| Plug Angle | |
| Product Group | Easy&Safe |

DIMENSIONS

| | |
|---------------------------|----------------|
| Product Net Width | 89 millimetre |
| Product Net Height | 120 millimetre |
| Product Net Length | 164 millimetre |
| Product Net Depth | 164 millimetre |
| Product Net Weight | 0.32 kilogram |

PACKAGING

| | |
|-----------------------------|----------------|
| Package Width | 134 millimetre |
| Package Height | 467 millimetre |
| Package Gross Weight | 1.6 kilogram |
| Package Length | 177 millimetre |
| Package Units | box 5 piece |