

232RS6

Wall mounted socket

2CMA193122R1000



Wall mounted socket, earthing sleeve position 6h, rated current 32A, IP44 splashproof, 2-poles+earth, frequency 50-60 Hz, color code Blue

GENERAL

Product Name	Wall mounted socket
Product ID	2CMA193122R1000
Function	Wall mounted socket
EAN	7392696931229
Catalog Description	Surface socket-outlet, 6h, 32A, IP44, 2P+E
Country of Origin	Czech Republic (CZ)
E-Number Finland	2421212
E-Number Norway	1542332
E-Number Sweden	E2416491
Standards	IEC 60309-1, -2
RoHS Status	Following EU Directive 2011/65/EU

TECHNICAL

Product Main Type	ERS
Color	Blue
Number of Poles	3
Clock Position	6Hour
Rated Current	32 ampere
Rated Voltage	200 ... 250 volt
Frequency	50 hertz 60 hertz
Degree of Protection	IP44
Cable Cross-Section	2.5...10 mm ²
Housing Material	Plastic (PA)
Plug Angle	
Product Group	Easy&Safe

DIMENSIONS

Product Net Width	85 millimetre
Product Net Height	118 millimetre
Product Net Length	163 millimetre
Product Net Depth	163 millimetre
Product Net Weight	0.3 kilogram

PACKAGING

Package Width	188 millimetre
Package Height	428 millimetre
Package Gross Weight	3 kilogram
Package Length	175 millimetre
Package Units	box 10 piece