

216RS6

Wall mounted socket

2CMA193098R1000



Wall mounted socket, earthing sleeve position 6h, rated current 16A, IP44 splashproof, 2-poles+earth, frequency 50-60 Hz, color code Blue

GENERAL

Product Name	Wall mounted socket
Product ID	2CMA193098R1000
Function	Wall mounted socket
EAN	73926969987
Catalog Description	Surface socket-outlet, 6h, 16A, IP44, 2P+E
Country of Origin	Czech Republic (CZ)
E-Number Finland	2421202
E-Number Norway	1542302
E-Number Sweden	E2416443
Standards	IEC 60309-1, -2
RoHS Status	Following EU Directive 2011/65/EU

TECHNICAL

Product Main Type	ERS
Color	Blue
Number of Poles	3
Clock Position	6Hour
Rated Current	16 ampere
Rated Voltage	200 ... 250 volt
Frequency	50 hertz 60 hertz
Degree of Protection	IP44
Cable Cross-Section	1.5...4 mm ²
Housing Material	Plastic (PA)
Plug Angle	
Product Group	Easy&Safe

DIMENSIONS

Product Net Width	66 millimetre
Product Net Height	91 millimetre
Product Net Length	117 millimetre
Product Net Depth	117 millimetre
Product Net Weight	0.22 kilogram

PACKAGING

Package Width	138 millimetre
Package Height	345 millimetre
Package Gross Weight	2.2 kilogram
Package Length	158 millimetre
Package Units	box 10 piece