



PANDUIT PART NO	BUNDLE DIAM		A in (mm)	B in (mm)	C in (mm)	D in (mm)	E in (mm)	F in (mm)	LOOP TENSILE lbs (N)	CROSS SECTION	WEIGHT lbs(g)/100 pcs	TIP STYLE
	MIN in (mm)	MAX in (mm)										
S4-18	.06 (1.5)	.87 (22)	.044 (1.1)	.10 (2.5)	.19 (4.8)	.154 (3.9)	.181 (4.6)	3.94 (100)	18 (80)	MINIATURE	0.054 (24.3)	CURVED
S6-18	.06 (1.5)	1.57 (40)	.044 (1.1)	.10 (2.5)	.19 (4.8)	.154 (3.9)	.188 (4.8)	6.29 (160)	18 (80)	MINIATURE	0.100 (45.5)	CURVED
S8-18	.06 (1.5)	2.09 (53)	.045 (1.2)	.10 (2.5)	.19 (4.8)	.157 (4.0)	.19 (4.8)	7.87 (200)	18 (80)	MINIATURE	0.124 (56.2)	CURVED
S6-40	.08 (2.0)	1.30 (33)	.045 (1.2)	.14 (3.6)	.26 (6.6)	.19 (4.8)	.268 (6.8)	5.51 (140)	40 (178)	INTERMEDIATE	0.148 (67.4)	CURVED
S8-40	.08 (2.0)	2.09 (53)	.045 (1.2)	.14 (3.6)	.256 (6.5)	.19 (4.8)	.268 (6.8)	7.87 (200)	40 (178)	INTERMEDIATE	0.195 (88.7)	CURVED
S12-40	.08 (2.0)	2.99 (76)	.045 (1.2)	.14 (3.6)	.26 (6.6)	.181 (4.6)	.264 (6.7)	11.81 (300)	40 (178)	INTERMEDIATE	.299 (135.9)	CURVED
S15-40	.08 (2.0)	4.02 (102)	.051 (1.3)	.14 (3.6)	.232 (5.9)	.181 (4.6)	.248 (6.3)	14.57 (370)	40 (178)	INTERMEDIATE	.377 (171.1)	CURVED

NOTE:
SEE WWW.PANDUIT.COM FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE, PART MATERIAL,
PART COLOR AND ANY THIRD PARTY RECOGNITION OR COMPLIANCE.

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	TITLE	ITEM REVISION NAME	DATASET FILE NAME	MATERIAL:	DRAWING NUMBER:	
00	3-15-17	ACC	JSWA	JADE	DRAWING RELEASED	012502	STRONGHOLD MINIATURE AND INTERMEDIATE TIES	00092FBI/00	00092FBI_DC/00	NYLON 6.6	00092FBI_DC	
							CUSTOMER DRAWING			PANDUIT		
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]					
							.x ± .1 [2.54] .xxx ± .020 [.51]					
							.xx ± .02 [.5] ANGLES ± 5 °					
								THIRD ANGLE PROJECTION				
							DRAWN BY: ACC	DATE: 2-22-17	CHK: JSWA	SCALE: N/A		SHT 1 OF 1
												A

D10100DA/20

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panduit:](#)

[S8-18-M0](#)