

332EC9

Industrial Connector

2CMA102042R1000

Industrial Connectors, 3P+E, 32A, 200 ... 250 V Clock
 Position Of Grounding Contact 9 hour Color code Blue



GENERAL

Product Name	Industrial Connector
Product ID	2CMA102042R1000
Function	Connector
EAN	739269428
Catalog Description	Industrial Connectors, 3P+E, 32A, 200 ... 250 V
Country of Origin	Czech Republic (CZ)
E-Number Finland	
E-Number Norway	
E-Number Sweden	E2416187
Standards	IEC 60309-1, -2
RoHS Status	Following EU Directive 2011/65/EU

DIMENSIONS

Product Net Width	79 millimetre
Product Net Height	93 millimetre
Product Net Length	182 millimetre
Product Net Depth	182 millimetre
Product Net Weight	0.28 kilogram

TECHNICAL

Product Main Type	EC
Color	Red
Number of Poles	4
Clock Position	9Hour
Rated Current	32 ampere
Rated Voltage	200 ... 250 volt
Frequency	50 hertz 60 hertz
Degree of Protection	IP44
Cable Cross-Section	2.5...6 mm ²
Housing Material	Plastic (PA)
Plug Angle	Straight
Product Group	Easy&Safe

PACKAGING

Package Width	154 millimetre
Package Height	378 millimetre
Package Gross Weight	2.8 kilogram
Package Length	182 millimetre
Package Units	box 10 piece