

363P6

Industrial Plug

2CMA166752R1000



Plug, earthing sleeve position 6h, rated current 63A, IP44 splashproof, 3-poles+earth, frequency 50-60 Hz, color code Red

GENERAL

| | |
|----------------------------|-----------------------------------|
| Product Name | Industrial Plug |
| Product ID | 2CMA166752R1000 |
| Function | Plug |
| EAN | 7392696667524 |
| Catalog Description | Plug, 6h, 63A, IP44, 3P+E |
| Country of Origin | Czech Republic (CZ) |
| E-Number Finland | 2421623 |
| E-Number Norway | 1565173 |
| E-Number Sweden | E2416226 |
| Standards | IEC 60309-1, -2 |
| RoHS Status | Following EU Directive 2011/65/EU |

TECHNICAL

| | |
|-----------------------------|------------------------|
| Product Main Type | TP |
| Color | Red |
| Number of Poles | 4 |
| Clock Position | 6Hour |
| Rated Current | 63 ampere |
| Rated Voltage | 380 ... 415 volt |
| Frequency | 50 hertz 60 hertz |
| Degree of Protection | IP44 |
| Cable Cross-Section | 4...16 mm ² |
| Housing Material | Thermoplastic (PBT) |
| Plug Angle | Straight |
| Product Group | Tough&Safe |

DIMENSIONS

| | |
|---------------------------|----------------|
| Product Net Width | 103 millimetre |
| Product Net Height | 103 millimetre |
| Product Net Length | 215 millimetre |
| Product Net Depth | 215 millimetre |
| Product Net Weight | 0.64 kilogram |

PACKAGING

| | |
|-----------------------------|----------------|
| Package Width | 114 millimetre |
| Package Height | 230 millimetre |
| Package Gross Weight | 0.72 kilogram |
| Package Length | 114 millimetre |
| Package Units | box 1 piece |