

216RAU6

Panel mounted socket

2CMA193218R1000



Panel mounted socket, earthing sleeve position 6h, rated current 16A, IP44 splashproof, unified flange, angled, 2-poles+earth, frequency 50-60 Hz, color code Blue

GENERAL

Product Name	Panel mounted socket
Product ID	2CMA193218R1000
Function	Panel mounted socket
EAN	7392696932189
Catalog Description	Socket-outlet, panel mounting, 6h, 16A, IP44, unified flange, angled, 2P+E
Country of Origin	Czech Republic (CZ)
E-Number Finland	2421261
E-Number Norway	1547402
E-Number Sweden	E2416637
Standards	IEC 60309-1, -2
RoHS Status	Following EU Directive 2011/65/EU

DIMENSIONS

Product Net Width	110 millimetre
Product Net Height	96 millimetre
Product Net Length	110 millimetre
Product Net Depth	110 millimetre
Product Net Weight	0.24 kilogram

TECHNICAL

Product Main Type	ERAU
Color	Blue
Number of Poles	3
Clock Position	6Hour
Rated Current	16 ampere
Rated Voltage	200 ... 250 volt
Frequency	50 hertz 60 hertz
Degree of Protection	IP44
Cable Cross-Section	1.5...4 mm ²
Housing Material	Plastic (PA)
Plug Angle	Angled
Product Group	Easy&Safe

PACKAGING

Package Width	154 millimetre
Package Height	378 millimetre
Package Gross Weight	2.4 kilogram
Package Length	182 millimetre
Package Units	box 10 piece