

316RS6

Wall mounted socket

2CMA193106R1000



Wall mounted socket, earthing sleeve position 6h, rated current 16A, IP44 splashproof, 3-poles+earth, frequency 50-60 Hz, color code Red

GENERAL

Product Name	Wall mounted socket
Product ID	2CMA193106R1000
Function	Wall mounted socket
EAN	73926969369
Catalog Description	Surface socket-outlet, 6h, 16A, IP44, 3P+E
Country of Origin	Czech Republic (CZ)
E-Number Finland	2421203
E-Number Norway	1542313
E-Number Sweden	E2416449
Standards	IEC 60309-1, -2
RoHS Status	Following EU Directive 2011/65/EU

TECHNICAL

Product Main Type	ERS
Color	Red
Number of Poles	4
Clock Position	6Hour
Rated Current	16 ampere
Rated Voltage	380 ... 415 volt
Frequency	50 hertz 60 hertz
Degree of Protection	IP44
Cable Cross-Section	1.5...4 mm ²
Housing Material	Plastic (PA)
Plug Angle	
Product Group	Easy&Safe

DIMENSIONS

Product Net Width	79 millimetre
Product Net Height	79 millimetre
Product Net Length	132 millimetre
Product Net Depth	132 millimetre
Product Net Weight	0.24 kilogram

PACKAGING

Package Width	154 millimetre
Package Height	378 millimetre
Package Gross Weight	2.4 kilogram
Package Length	182 millimetre
Package Units	box 10 piece