

432P6W

Industrial Plug

2CMA166524R1000



Plug, earthing sleeve position 6h, rated current 32A, IP67 watertight, 3-poles+neutral+earth, frequency 50-60 Hz, color code Red

GENERAL

Product Name	Industrial Plug
Product ID	2CMA166524R1000
Function	Plug
EAN	7392696665247
Catalog Description	Plug, 6h, 32A, IP67, 3P+N+E
Country of Origin	Czech Republic (CZ)
E-Number Finland	2421646
E-Number Norway	2416277
E-Number Sweden	E2416277
Standards	IEC 60309-1, -2
RoHS Status	Following EU Directive 2011/65/EU

TECHNICAL

Product Main Type	TP
Color	Red
Number of Poles	5
Clock Position	6Hour
Rated Current	32 ampere
Rated Voltage	200/346 ... 240/415 volt
Frequency	50 hertz 60 hertz
Degree of Protection	IP67 IP69
Cable Cross-Section	2.5...6 mm ²
Housing Material	Thermoplastic (PBT)
Plug Angle	Straight
Product Group	Tough&Safe

DIMENSIONS

Product Net Width	101 millimetre
Product Net Height	101 millimetre
Product Net Length	161 millimetre
Product Net Depth	161 millimetre
Product Net Weight	0.405 kilogram

PACKAGING

Package Width	135 millimetre
Package Height	200 millimetre
Package Gross Weight	0.475 kilogram
Package Length	140 millimetre
Package Units	box 1 piece