



Receptacle Holder

Plug Holder

Shell Size		Recommended Torque (+/- 5 Inch-Pounds)		A Dia. Max.	B Dia. Max.	C Dim. Max.
Com'l	Mil. Ref.	Metal	Composite			
09	A	60	35	.577 (14.7)	.438 (11.1)	1.031 (26.2)
11	B	80	35	.709 (18.0)	.566 (14.4)	1.031 (26.2)
13	C	110	40	.829 (21.1)	.678 (17.2)	1.031 (26.2)
15	D	120	40	.954 (24.2)	.803 (20.4)	1.031 (26.2)
17	E	120	40	1.107 (28.1)	.928 (23.6)	1.031 (26.2)
19	F	120	40	1.190 (30.2)	1.033 (26.2)	1.031 (26.2)
21	G	140	80	1.315 (33.4)	1.158 (29.4)	1.031 (26.2)
23	H	140	80	1.440 (36.6)	1.283 (32.6)	1.031 (26.2)
25	J	140	80	1.565 (39.8)	1.408 (35.8)	1.031 (26.2)

NOTES

1. Metric dimensions (mm) are indicated in parentheses.
2. Material: Case hardened carbon steel with electroless nickel finish.
3. Receptacle and plug holder drives: 1/4" - Shell sizes 09, 11 and 13; 3/8" - Shell sizes 15 and up.
4. Composite values apply when using Glenair 600-091 and 600-007 tools.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Glenair:

[600H005-15RN](#) [600H005-19PN](#) [600H005-25RC](#) [600H005-11PE](#) [600H005PC-KIT](#) [600H005-33RN](#) [600H005-23RA](#)
[600H005-11RN](#) [600H005-25LRE](#) [600H005-19PB](#) [600H005-21PD](#) [600H005-13PN](#) [600H005-09PB](#) [600H005-13PC](#)
[600H005-11PB](#) [600H005-21RC](#) [600H005-09RA](#) [600H005-11RB](#) [600H005-15PE](#) [600H005-25PN](#) [600H005-25LPN](#)
[600H005-25LPB](#) [600H005-17PA](#) [600H005-25PC](#) [600H005-23PA](#) [600H005-17PD](#) [600H005-19RA](#) [600H005-19RN](#)
[600H005-23PN](#) [600H005-17RA](#) [600H005-19PA](#) [600H005-11RE](#) [600H005-11PA](#) [600H005PA-KIT](#) [600H005-17PC](#)
[600H005-13RC](#) [600H005-15RB](#) [600H005-11RD](#) [600H005-19RC](#) [600H005-25RN](#) [600H005PB-KIT](#) [600H005RN-KIT](#)
[600H005-13RN](#) [600H005-13PB](#) [600H005-09PA](#) [600H005-13PE](#) [600H005-13RB](#) [600H005-09RN](#) [600H005-21RU](#)
[600H005-21RA](#) [600H005-11PD](#) [600H005-25LRB](#) [600H005-25RE](#) [600H005-13PA](#) [600H005-25PB](#) [600H005-15PC](#)
[600H005-09PN](#) [600H005-23RN](#) [600H005-21PB](#) [600H005-23PD](#) [600H005-13PD](#) [600H005-19PD](#) [600H005-11PN](#)
[600H005-11PC](#) [600H005-25PA](#) [600H005-09PC](#) [600H005-17RB](#) [600H005-09RB](#) [600H005-25LRA](#) [600H005-17PU](#)
[600H005-15PA](#) [600H005-21PC](#) [600H005-25LRC](#) [600H005-25RB](#) [600H005-25LPA](#) [600H005-17PN](#) [600H005-25LPE](#)
[600H005PU-KIT](#) [600H005-25PE](#) [600H005-21PN](#) [600H005-15RE](#) [600H005-13RE](#) [600H005-11RA](#) [600H005-23PU](#)
[600H005-25RA](#) [600H005-15RA](#) [600H005-17PB](#) [600H005-13RA](#) [600H005-11RC](#) [600H005-17RN](#) [600H005-17PE](#)
[600H005-19RB](#) [600H005-25PD](#) [600H005-23PB](#) [600H005-21PA](#) [600H005-15PN](#) [600H005-37RN](#) [600H005-21RN](#)
[600H005-25LPC](#) [600H005-15PB](#)