



Notes:

- 1. Color: Natural;
- 2. RoHS Compliant;
- 3. Bottom Hole: $\text{Ø}4.75 \pm 0.08 \text{mm}$,
Panel Thickness: 1.5-1.6mm.

Part No.	Part Name	Part No.	Part Name	A
41204	8G820V41204	41771	8G820V41771	6.4
41205	8G820V41205	41772	8G820V41772	7.9
41206	8G820V41206	41773	8G820V41773	9.5
41207	8G820V41207	41774	8G820V41774	11.1
41208	8G820V41208	41775	8G820V41775	12.7
41209	8G820V41209	41776	8G820V41776	14.3
41210	8G820V41210	41777	8G820V41777	15.9
Material: PA66 UL94 V2		Material: PA66 UL94 V0		

DREMEC Befestigungselemente GmbH

DATE 2020.03.19

DIMENSION TOLERANCE

TITLE REVERSE LOCKING CIRCUIT BOARD SUPPORT - ROUND HOLE SPACER SCALE FIT $L \leq 4$ ± 0.10

PART NAME 8G820V41204 MOLD NO. S0375 DRAW PLK UNIT MM $4 < L \leq 15$ ± 0.20

PART NO. SEE TABLE MATERIAL SEE TABLE DESIGN PLK VERSION A0 $15 < L \leq 50$ ± 0.30

DWG NO. E4130 COLOR SEE NOTES APPROVAL FDL VIEW  $50 < L \leq 100$ ± 0.40